

Easy AI. Fast ROI.

Right-Sized. Real-Time. Ready.

The AI Adoption Gap

AI is too expensive

Traditional solutions require large upfront investment.

Cloud isn't always viable

Data privacy & compliance restrict use.

It takes too long to see results

AI projects often stall in deployment.

You need a full team to run it

Complexity puts strain on internal IT.

Meet the Solution

- Built for departments, not data centers
- Affordable AI performance
- Powered by Intel® Xeon® 6 CPUs — no expensive GPUs needed
- Integrated with NetApp's trusted ONTAP® storage and OPEA software stack
- Backed by Arrow's AI Accelerator team, on-hand for anything you need
- Secure, on-site processing for data privacy and compliance

Optimized for Departments & Edge Deployments

e.g., <12U rack space, <20 concurrent users)

Industry Use Cases

Manufacturing
Predict machine failures, reduce defects, streamline ops.

Legal
Summarize contracts, maintain compliance, protect confidentiality.

Public Sector
Analyze case data securely, operate without cloud.

Value Pillars

Affordable

Right-sized for departments

Simple

Plug-and-play, deploy fast, minimal IT burden

Secure

Local inferencing, full control of your data

Impactful

Built-in workflows get you results, fast

Integrated

Works with your data, in your environment

Scalable

Start small, grow smart

Before AIPOd Mini with Intel

- Complex, expensive AI stacks
- Cloud latency and risk
- Centralized decision bottlenecks
- Projects stuck in POC purgatory

VS

After AIPOd Mini with Intel

- Simple, integrated platform
- On-site, real-time responses
- Local, departmental insights
- Rapid time-to-value

Ready to make AI practical?

Discover how the **NetApp AIPOd Mini with Intel** can bring AI to life securely, affordably and on your terms.

Talk to a NetApp AI expert

See how it compares

